



VSR910CUSPD

Design 50, 10 Way HI 100A Sw 2*100A 30mA RCCB Type A SPD

Technical Characteristics

Fixing mode	flush-mounting
Rated current	100 A
Depth of installed product	105 mm
Height of installed product	284 mm
Width of installed product	467 mm
Number of modules	10
Type of door closing	non keylock
Interlockable	No
Colour	RAL 9010
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Type of surface treatment	Galvanised
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC