



WFCC50NBNB

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	45 A

Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	black
Material	stainless steel
Surface appearance	matt
Type of surface treatment	Nickel-plated

Connection

Type of connection	Screw connection
--------------------	------------------

Safety

Protection index IP	IP20
Protection	to protect downstream loads

Use conditions

Insert	insert, black
--------	---------------