



WFCC50NBSB



45A Cooker Control Unit Brushed Steel Black Insert

Technical characteristics

Electric current

Rated current	45 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Connection

Conductor cross-section	16 - 16 mm ²
-------------------------	-------------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Height	86 mm
--------	-------

Width	146 mm
-------	--------

Depth	39.60 mm
-------	----------

Materials

Colour	Stainless steel
--------	-----------------

Surface finish	Mat
----------------	-----

Material	Stainless steel
----------	-----------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	Yes
------------------	-----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads
