



WFCC50NPBW

## Technical characteristics

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	45 A

### Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

### Cover, door

Cover	Full cover plate
-------	------------------

### Materials

Material	stainless steel
Type of surface treatment	Anodised

### Connection

Type of connection	Screw connection
--------------------	------------------

### Safety

Protection index IP	IP20
Protection	to protect downstream loads

### Use conditions

Insert	insert white
--------	--------------