



WFCC50NPSB



45A Cooker Control Unit Polished Steel Black Insert

Technical characteristics

Electric current

Rated current 45 A

Voltage

Rated voltage 250 V

Connection

Conductor cross-section 16 - 16 mm²

Safety

Ingress Protection (IP) class IP20

Dimensions

Height 86 mm

Width 146 mm

Depth 39.60 mm

Materials

Colour Silver

Surface finish Glossy

Material Stainless steel

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp Yes

Accessories

Has labelling field No

Capacity

Number of modules 0

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads
