



WFCC50NPSB

45A Cooker Control Unit Polished Steel Black Insert

Technical characteristics

Architecture

|             |                |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Rated current   | 45 A     |

Dimensions

|        |         |
|--------|---------|
| Depth  | 39.6 mm |
| Height | 86 mm   |
| Width  | 146 mm  |

Cover, door

|       |                  |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

Materials

|                           |       |
|---------------------------|-------|
| Type of surface treatment | Other |
|---------------------------|-------|

Cable

|        |                              |
|--------|------------------------------|
| Wiring | with double earth connection |
|--------|------------------------------|

Scope of delivery

|           |                                   |
|-----------|-----------------------------------|
| Component | with 2 fixing screws M3.5 x 20 mm |
|-----------|-----------------------------------|

Safety

|                     |                             |
|---------------------|-----------------------------|
| Protection index IP | IP20                        |
| Protection          | to protect downstream loads |

Use conditions

|        |               |
|--------|---------------|
| Insert | insert, black |
|--------|---------------|