



WFCC50NPSW

45A Cooker Control Unit Polished Steel White Insert

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	45 A

Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Type of surface treatment	Other
---------------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
Protection	to protect downstream loads

Use conditions

Insert	insert white
--------	--------------