



WFDP50NBSW



## 50A Double Pole Switch 1 Gang with LED Indicator Brushed Steel White Insert

### Technical characteristics

#### Electric current

Rated current 50 A

#### Installation, mounting

Mounting on Flush mounting

#### Voltage

Rated voltage 250 V

#### Materials

Colour Stainless steel

Surface finish Mat

Material Stainless steel

Treatment Brushed

#### Identification

Assembly arrangement Basic element with full cover plate

#### Connectivity

Mounting type Screw mounting

#### Controls and indicators

Number of buttons 1

#### Dimensions

Built-in depth 29.10 mm

#### Safety

Ingress Protection (IP) class IP20

#### Architecture

Control/operation element Single rocker

#### Texts

Lighting With control LED for ON

Switch mode 2-pole