



WFDP84BSB



20A Double Pole Switch Brushed Steel Black Insert

Technical characteristics

Electric current

Rated current 20 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Stainless steel

Surface finish Mat

Material Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Built-in depth 27.90 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole