



WFDP84FOBSW



## 20A Double Pole Switch with Flex Outlet Brushed Steel White Insert

### Technical characteristics

#### Electric current

Rated current	20 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Built-in depth	27.90 mm
----------------	----------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole