



WFS51BNB

## Technical characteristics

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	5 A

### Dimensions

Depth	25 mm
Height	86 mm
Width	86 mm

### Cover, door

Cover	Full cover plate
-------	------------------

### Materials

Colour	black
Material	stainless steel
Surface appearance	matt
Type of surface treatment	Nickel-plated

### Connection

Type of connection	screw
--------------------	-------

### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

### Use conditions

Insert	insert, black
--------	---------------