



WFSO100BSB

### 115/230V Shaver Outlet Brushed Steel Black Insert

#### Technical characteristics

##### Architecture

Number of poles 2pole

##### Main electrical features

Nominal voltage 250 V AC

Rated current  $\approx 87...174$  mA

##### Dimensions

Depth 54.5 mm

Height 146 mm

Width 86 mm

##### Cover, door

Cover Full cover plate

##### Materials

Surface appearance matt

##### Connection

Type of connection screw

Type of connection with screw terminals

##### Cable

Wiring with double earth connection

##### Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm

##### Safety

Protection Enhanced contact protection

##### Use conditions

Insert insert, black