



WFSO100BSB

115/230V Shaver Outlet Brushed Steel Black Insert

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole

Main electrical features

Nominal voltage	250 V AC
Rated current	≈ 87...174 mA

Dimensions

Depth	54.5 mm
Height	146 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed

Connection

Type of connection	screw
Type of connection	with screw terminals

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert, black
--------	---------------