



WFSO100BSW

## 115/230V Shaver Outlet Brushed Steel White Insert

### Technical characteristics

#### Architecture

Number of poles 2pole

#### Main electrical features

Nominal voltage 250 V AC

Rated current  $\approx 87...174$  mA

#### Dimensions

Depth 54.5 mm

Height 146 mm

Width 86 mm

#### Cover, door

Cover Full cover plate

#### Materials

Surface appearance matt

#### Connection

Type of connection with screw terminals

#### Cable

Wiring with double earth connection

#### Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm

#### Safety

Protection Enhanced contact protection

#### Use conditions

Insert insert white