



WFSO100PSW

## 115/230V Shaver Outlet Polished Steel White Insert

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
Number of poles	2pole

#### Main electrical features

Nominal voltage	250 V AC
Rated current	≈ 87...174 mA

#### Dimensions

Depth	54.5 mm
Height	146 mm
Width	86 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Materials

Type of surface treatment	Other
---------------------------	-------

#### Cable

Wiring	with double earth connection
--------	------------------------------

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm
-----------	-----------------------------------

#### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

#### Use conditions

Insert	insert white
--------	--------------