



WFSS81BSB



## 13A 1 Gang Double Pole Switched Socket Brushed Steel Black Insert

### Technical characteristics

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Dimensions

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	25.80 mm
-------	----------

#### Materials

Colour	Stainless steel
--------	-----------------

Surface finish	Mat
----------------	-----

Material	Stainless steel
----------	-----------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

#### Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

#### Texts

Imprint	Without imprint
---------	-----------------

---

Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

---