



WFSS81BSW

13A 1 Gang Double Pole Switched Socket Brushed Steel White Insert

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

Dimensions

Depth	25.8 mm
Height	86 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Surface appearance	matt
Type of surface treatment	brushed

Cable

Wiring	with earth connection
--------	-----------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert white
--------	--------------