



WFSS81PBW



**13A 1 Gang Double Pole Switched Socket Polished Brass White Insert**

**Technical Characteristics**

|   |                                   |
|---|-----------------------------------|
| Fixing mode                                   | flush-mounting                    |
| Nominal voltage                               | 250 V                             |
| Rated voltage                                 | 220...230 V AC                    |
| Rated current                                 | 13 A                              |
| Rated current                                 | 13 A                              |
| Depth   | 25.8 mm                           |
| Height  | 86 mm                             |
| Width   | 86 mm                             |
| Number of modules                             | 0                                 |
| Cover   | Full cover plate                  |
| Colour  | brass optics                      |
| Material                                      | stainless steel                   |
| Surface appearance                            | glossy                            |
| Type of surface treatment                     | Anodised                          |
| Colour syntax: Colour                         | brass                             |
| Imprint                                       | without imprint                   |
| Type of connection                            | screw                             |
| Wiring  | with earth connection             |
| Component                                     | with 2 fixing screws M3.5 x 20 mm |
| Protection index IP                           | IP20                              |
| Protection                                    | Enhanced contact protection       |
| Insert  | insert white                      |
| Designation syntax: Core designation/function | socket outlet                     |