



WFSS81PBW

## Technical characteristics

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

### Dimensions

Depth	25.8 mm
Height	86 mm
Width	86 mm

### Cover, door

Cover	Full cover plate
-------	------------------

### Materials

Type of surface treatment	Anodised
---------------------------	----------

### Cable

Wiring	with earth connection
--------	-----------------------

### Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm
-----------	-----------------------------------

### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

### Use conditions

Insert	insert white
--------	--------------