



WFSS81PSB



### 13A 1 Gang Double Pole Switched Socket Polished Steel Black Insert

#### Technical characteristics

##### Electric current

Rated current	13 A
---------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Dimensions

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	25.80 mm
-------	----------

##### Materials

Colour	Silver
--------	--------

Surface finish	Glossy
----------------	--------

Material	Stainless steel
----------	-----------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	0
-------------------	---

##### Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection