



WFSS82BNB-USBS

**13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Black Nickel**

**Technical characteristics**

**Architecture**

Fixing mode	flush-mounting
-------------	----------------

**Main electrical features**

Nominal voltage	250 V
Rated voltage	220...230 V AC

**Dimensions**

Depth	39.1 mm
Height	86 mm
Width	146 mm

**Cover, door**

Cover	Full cover plate
-------	------------------

**Materials**

Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed

**Connection**

Type of connection	screw
--------------------	-------

**Safety**

Protection index IP	IP20
Protection	Enhanced contact protection

**Use conditions**

Insert	insert, black
--------	---------------