



WFSS82BSB-USBSAC

DP Switched Socket 13A 2G USB A+C ports Brushed Steel Black Flat

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	230 V
Rated voltage	220...230 V AC

Dimensions

Depth	16 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert, black
--------	---------------