



WFSS82BSW

### 13A 2 Gang Double Pole Switched Socket Brushed Steel White Insert

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

##### Dimensions

Depth 29 mm

Height 86 mm

Width 146 mm

##### Cover, door

Cover Full cover plate

##### Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

##### Connection

Type of connection screw

##### Cable

Wiring with double earth connection

##### Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm

##### Safety

Protection index IP IP20

Protection Enhanced contact protection

##### Use conditions

Insert insert white