



WFSS82BSW-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Brushed Steel White sh

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

Dimensions

Height	86 mm
Width	146 mm
Depth	39.10 mm
Built-in depth flush-mounted boxes	25 mm

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting
Connector/plug type USB	A

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	With imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection