



WFSS82BSW-USBSAC

DP Switched Socket 13A 2G USB A+C ports Brushed Steel White Flat

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 220...240 V AC

Dimensions

Depth 16 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

Connection

Type of connection screw

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm

Safety

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Insert insert white