



WFSS82PBB-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Polished Brass Black

Technical characteristics

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Main electrical features

| | |
|-----------------|----------------|
| Nominal voltage | 250 V |
| Rated voltage | 220...230 V AC |

Dimensions

| | |
|--------|---------|
| Depth | 39.1 mm |
| Height | 86 mm |
| Width | 146 mm |

Cover, door

| | |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

Materials

| | |
|---------------------------|-----------------|
| Material | stainless steel |
| Type of surface treatment | Anodised |

Connection

| | |
|--------------------|-------|
| Type of connection | screw |
|--------------------|-------|

Safety

| | |
|---------------------|-----------------------------|
| Protection index IP | IP20 |
| Protection | Enhanced contact protection |

Use conditions

| | |
|--------|---------------|
| Insert | insert, black |
|--------|---------------|