



WFSS82PSB-USBSAC



**DP Switched Socket 13A 2G USB A+C ports Polished Steel Black Flat**

**Technical characteristics**

**Electric current**

Rated current	13 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Nominal voltage	230 - 230 V
-----------------	-------------

**Connectivity**

Connector/plug type USB	AC
Type of connection	Screw terminal
Mounting type	Screw mounting

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Dimensions**

Built-in depth flush-mounted boxes	25 mm
Height	86 mm
Width	146 mm
Depth	16 mm

**Materials**

Surface finish	Glossy
Material	Stainless steel

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

**Texts**

Imprint	With imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection