



WFSS82PSW



## 13A 2 Gang Double Pole Switched Socket Polished Steel White Insert

### Technical characteristics

#### Electric current

Rated current 13 A

#### Voltage

Rated voltage 250 V

Nominal voltage 250 - 250 V

#### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

#### Safety

Ingress Protection (IP) class IP20

#### Dimensions

Height 86 mm

Width 146 mm

Depth 29 mm

#### Materials

Colour Silver

Surface finish Glossy

Material Stainless steel

#### Installation, mounting

Mounting on Flush mounting

#### Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

#### Accessories

Has labelling field No

#### Capacity

Number of modules 0

#### Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection