



WFSSU83BNB

Technical characteristics

Main electrical features

| | |
|---------------|----------|
| Frequency | 50/60 Hz |
| Rated current | 13 A |

Fuse

| | |
|------|------------------------------|
| Fuse | with ceramic fine fuse F 13A |
|------|------------------------------|

Dimensions

| | |
|--------|---------|
| Depth | 30.3 mm |
| Height | 86 mm |
| Width | 86 mm |

Cable

| | |
|--------|------------------------------|
| Wiring | with double earth connection |
|--------|------------------------------|

Scope of delivery

| | |
|-----------|-----------------------------------|
| Component | with 2 fixing screws M3.5 x 20 mm |
|-----------|-----------------------------------|

Equipment

| | |
|----------|--|
| Lighting | without lighting (cannot be illuminated) |
|----------|--|

Safety

| | |
|------------|-----------------------------|
| Protection | to protect downstream loads |
|------------|-----------------------------|

Use conditions

| | |
|--------|---------------|
| Insert | insert, black |
|--------|---------------|