



WMCC50

13A Double Pole Switched Socket Outlet with Cooker Control Unit

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 45 A

Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour white

Type of surface treatment untreated

Connection

Type of connection Screw connection

Safety

Protection index IP IP20

Protection to protect downstream loads