



WMCC50

13A Double Pole Switched Socket Outlet with Cooker Control Unit

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	45 A

Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

Materials

Colour	white
Type of surface treatment	untreated

Connection

Type of connection	Screw connection
--------------------	------------------

Safety

Protection index IP	IP20
Protection	to protect downstream loads