



WMCC50N

## Cooker Control Unit with LED Indicator

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 45 A

#### Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

#### Cover, door

Cover Full cover plate

#### Materials

Colour white

Material duroplastic

Type of surface treatment untreated

#### Connection

Type of connection Screw connection

#### Safety

Protection index IP IP20

Protection to protect downstream loads