



WMDP84NG

20A Double Pole Switch with LED Indicator & Grey Plate

Technical Characteristics

Switch mode	2pole
Frequency	50/60 Hz
Depth	32.8 mm
Height	86 mm
Width	86 mm
Colour	white
Material	Urea-formaldehyde
Imprint	with clear terminal markings
Component	with 2 fixing screws M3.5 x 30 mm
Lighting	with control LED for ON
Designation syntax: Core designation/function	Switch