



WMGS12BSB



20A 2 Way Single Pole Switch Brushed Steel Black Insert

Technical characteristics

Electric current

| | |
|-------------------|------|
| Switching current | 20 A |
| Rated current | 20 A |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-----------------|
| Colour | Stainless steel |
| Surface finish | Mat |
| Material | Stainless steel |
| Treatment | Brushed |

Identification

| | |
|----------------------|----------------------------------------|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|----------------------------------------|

Connectivity

| | |
|---------------|-------------------|
| Mounting type | Snapp-on mounting |
|---------------|-------------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|----------------|----------|
| Built-in depth | 13.10 mm |
|----------------|----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Texts

| | |
|-------------|------------------------------------------|
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole |