



WMGS16



20A Intermediate Switch

Technical characteristics

Electric current

Rated current	20 A
---------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Snapp-on mounting
---------------	-------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Built-in depth	13.10 mm
----------------	----------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	Intermediate