



WMGSD1S



Grid Slave Switch

Technical characteristics

Voltage

Operating voltage	240 - 240 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
Material	Urea formaldehyde

Dimensions

Height	60 mm
Width	24 mm
Depth	40 mm

Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

Capacity

Number of modules	1
-------------------	---

Texts

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Installation mode	Installation in surface-mounted or flush-mounted housings
Type of connection	With screw terminals
Operation and control	No Bluetooth interface