



WMGSD1T



## Grid Dimmer Switch Trailing Edge

### Technical characteristics

#### Voltage

Operating voltage 240 - 240 V

#### Frequency

Frequency 50 - 60 Hz

#### Materials

Colour White

Material Urea formaldehyde

#### Dimensions

Height 60 mm

Width 24 mm

Depth 40 mm

#### Architecture

Control/operation element Push & rotative switch

#### Capacity

Number of modules 1

#### Texts

Dimming principle Phase cut-off

Installation mode Installation in surface-mounted or flush-mounted housings

Operation and control No Bluetooth interface

Type of connection With screw terminals