



WMGSDP2

## 20A 1 Way Double Pole Switch

### Technical characteristics

#### Configuration

|             |       |
|-------------|-------|
| Switch mode | 2pole |
|-------------|-------|

#### Main electrical features

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

#### Dimensions

|       |       |
|-------|-------|
| Depth | 24 mm |
|-------|-------|

|        |       |
|--------|-------|
| Height | 59 mm |
|--------|-------|

|       |       |
|-------|-------|
| Width | 25 mm |
|-------|-------|

#### Materials

|        |       |
|--------|-------|
| Colour | white |
|--------|-------|

|          |                   |
|----------|-------------------|
| Material | Urea-formaldehyde |
|----------|-------------------|

#### Equipment

|          |  |
|----------|--|
| Lighting | without lighting (cannot be illuminated) |
|----------|--|

#### Use conditions

|        |              |
|--------|--------------|
| Insert | insert white |
|--------|--------------|