



WMGSDP2

20A 1 Way Double Pole Switch

Technical Characteristics

Switch mode	2pole
Frequency	50/60 Hz
Rated current	20 A
Depth	24 mm
Height	59 mm
Width	25 mm
Colour	white
Material	Urea-formaldehyde
Imprint	with clear terminal markings
Lighting	without lighting (cannot be illuminated)
Insert	insert white
Designation syntax: Core designation/function	Switch