



WMGSDP2B/HW



**20A 1 Way Double Pole Switch Marked 'HOT WATER' Black**

**Technical characteristics**

**Electric current**

Switching current	20 A
Rated current	20 A

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	Black
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element with central cover plate
----------------------	--

**Connectivity**

Mounting type	Snapp-on mounting
---------------	-------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Built-in depth	13.10 mm
----------------	----------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Texts**

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole