



WMGSDP2/PH



## 20A 1 Way Double Pole Switch Marked 'PLINTH HEATER'

### Technical characteristics

#### Electric current

Switching current	20 A
Rated current	20 A

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

#### Connectivity

Mounting type	Snapp-on mounting
---------------	-------------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Built-in depth	13.10 mm
----------------	----------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Texts

Lighting	With control LED for ON
Switch mode	2-pole