



WMMSAT



## Single Satellite F Connector Euromodule White

### Technical characteristics

#### Connectivity

Mounting type	Snapp-on mounting
---------------	-------------------

#### Attenuation

Tap loss at 2150 MHz	0.60 dB
----------------------	---------

#### Connection

Connector/plug type	Direct socket
---------------------	---------------

#### Frequency

Frequency bandwidth	5 - 2,300 MHz
---------------------	---------------

#### Equipment

Number of outputs	1
-------------------	---

#### Materials

Material	Urea formaldehyde
----------	-------------------

Colour	White
--------	-------

#### Dimensions

Depth	30.50 mm
-------	----------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------