



WMMTVFB



Single IEC Female Euromodule Black

Technical characteristics

Connectivity

Mounting typeSnapp-on mounting

Attenuation

Tap loss at 860 MHz0.30 dB

Connection

Connector/plug typeDirect socket

Frequency

Frequency bandwidth5 - 860 MHz

Equipment

Number of outputs1

Materials

MaterialUrea formaldehyde

ColourWhite

Dimensions

Depth24 mm

Installation, mounting

Mounting onFlush mounting

Identification

Assembly arrangementBasic element with full cover plate