



WMPS12RB



Push Switch with Bell Symbol

Technical characteristics

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Number of poles	2
-----------------	---

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Coated
Transparent	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Depth	24 mm
-------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	Without imprint
Installation mode	For flush-mounted and hollow wall mounting
Switch mode	NO contact