



WMPS32



10AX 3 Gang 2 Way Wall Switch

Technical characteristics

Electric current

Switching current	10 A
Rated current	10 A

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	3
-------------------	---

Dimensions

Built-in depth	12 mm
----------------	-------

Safety

Ingress Protection (IP) class	IP21
-------------------------------	------

Architecture

Control/operation element	Triple rocker
---------------------------	---------------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way