



WMPS62



## 10AX 6 Gang 2 Way Wall Switch

### Technical characteristics

#### Electric current

Switching current	10 A
Rated current	10 A

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	6
-------------------	---

#### Dimensions

Built-in depth	12 mm
----------------	-------

#### Safety

Ingress Protection (IP) class	IP21
-------------------------------	------

#### Architecture

Control/operation element	6-gang rocker
---------------------------	---------------

#### Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way