



WMS82

### 13A 2 Gang Unswitched Socket Dual Earth

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

##### Dimensions

Depth 26.2 mm

Height 86 mm

Width 146 mm

##### Cover, door

Cover Full cover plate

##### Materials

Colour white

Type of surface treatment untreated

##### Connection

Type of connection screw

##### Safety

Protection index IP IP20

Protection Enhanced contact protection