



WMSS81



1 Gang Double Pole Switched Socket

Technical characteristics

Electric current

| | |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Dimensions

| | |
|--------|-------|
| Height | 86 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 86 mm |
|-------|-------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

| | |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

| | |
|----------|-------------------|
| Material | Urea formaldehyde |
|----------|-------------------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

| | |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
|-----------------------------------|------------------|

| | |
|------------------------|----|
| Rotated central insert | No |
|------------------------|----|

| | |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

| | |
|---------------------------------|----|
| With round protective earth pin | No |
|---------------------------------|----|

| | |
|------------------|----|
| With signal lamp | No |
|------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Texts

| | |
|------------|-----------------------------|
| Imprint | Without imprint |
| Cover | Full cover plate |
| Wiring | With earth connection |
| Protection | Enhanced contact protection |