



WMSS81



## 1 Gang Double Pole Switched Socket

### Technical characteristics

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

#### Dimensions

Height	86 mm
Width	86 mm

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Functions</b>	
With orientation lighting	No
With function lighting	No
<b>Texts</b>	
Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection