



WMSS81G



## 1 Gang Double Pole Switched Socket with Grey Face Plate

### Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A
Depth	25.8 mm
Height	86 mm
Width	86 mm
Number of modules	0
Cover	Full cover plate
Colour	black
Material	duroplastic
Surface appearance	glossy
Type of surface treatment	untreated
Colour syntax: Colour	black
Imprint	without imprint
Type of connection	screw
Wiring	with earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Designation syntax: Core designation/function	socket outlet